

**CF-ECO LAB/F9 and CF-ECO LAB/F9+HEPA H13 are Complete Units with Fan and Filter. They have a built in Jet-Pulse Cleaning System for the F9 Filter. Suitable for 1-2 Flexi Extraction-Arms d.160mm, or 4-8 Flexa/Chemicus Extraction-Arms dia.75mm or 100mm**

### **CF-ECO LAB/F9. Fume and Light Dust.**

It is equipped with a 9m<sup>2</sup> F9 Filter Cartridge and a built in Fan with aluminium impeller. The legs are 0.5m. The air volume is ca.1800m<sup>3</sup>/h at the dia.199mm Inlet.

### **CF-ECO LAB/F9+HEPA H13. Light Fume/Fine Dust.**

It is equipped with a F9 Filter Cartridge (9m<sup>2</sup>) and a HEPA H13 (9m<sup>2</sup>) Filter Box. The F9 Filter has a built in Jet-Pulse Cleaning System. The F9 Filter (9m<sup>2</sup>) works as a prefilter to increase the lifetime of the HEPA H13 Filter. The Airvolume is ca.1400m<sup>3</sup>/h at the dia.199mm Inlet.

The unit has more than 99.995% efficiency and is also cleaning the room from Virus and Bacteria.

### **Jet-Pulse Cleaning of F9 Cartridge.**

All CF-ECO Extractor Filters have a built in pneumatic cleaning system. When the extraction volume has become too low you clean the F9 Cartridge with the Jet-Pulse. Takes just a few minutes. Then take out the dust bin and empty it.

The CF-ECO is now back to normal Extraction volume again. The F9 Filter Cartridge can be cleaned up to 100 times.

**Capacity.** 4-8 Flexa/Chemikus Extraction-Arms (d.75 or 100mm) can be connected to a CF-ECO LAB Extractor Filter or 1-2 dia.160mm Flexi Extraction-Arms (Max. 2m Length).

**Installation.** The inlet is dia.199mm. Use d.200mm Vertical/ Horizontal ducting from the CF-ECO LAB Unit. Go with dia. 75/100mm duct down to Flexa/Chemikus Extraction-Arms or dia.160mm duct down to Flexi Extraction-Arms.



**Plymoth is always a Step Ahead - but Not Expensive!**

	Art. No.
CF-ECO LAB/F9. ~1/1.1kW/220V/50Hz. F9 Filter(9m <sup>2</sup> ). Inlet 199mm. 4 Legs (0.5m).	P-1014
CF-ECO LAB/F9. ~3/1.1kW/400V/50Hz. F9 Filter(9m <sup>2</sup> ). Inlet 199mm. 4 Legs (0.5m)	P-1015
CF-ECO LAB/F9+HEPA H13 ~1/1.1Kw/220V/50Hz. 9m <sup>2</sup> +9m <sup>2</sup> . Inlet 199mm. 4 Legs (0.5m)	P-1016
CF-ECO LAB/F9+HEPA H13 ~3/1.1Kw/400V/50Hz. 9m <sup>2</sup> +9m <sup>2</sup> . Inlet 199mm. 4 Legs (0.5m)	P-1017
F9 Replacement Filter Cartridge 9m <sup>2</sup> . For CF/MF/WF-ECO, CF-ECO Lab, Grinder	P-541
HEPA H13 Filter Box 9m <sup>2</sup> . For CF-ECO, CF-ECO LAB, MF-ECO, MF-Filter Tables .	P-544

J.Plymoth AB, Trarydsalle´n 4E, 287 72 TRARYD, Sweden.  
Tel. +46 (0) 40 700 15. E-Mail: info@plymoth.com www.plymoth.com